

Pneumatic Scale Corporation Pneumacap-Series 8-head Capper

Mfg: Pneumatic Scale Corporation

Model: Pneumacap 3338

Stock No. OI280.

Serial No. 20030

Pneumatic Scale Corporation Pneumacap-Series 8-head Capper. Model: Pneumacap 3338. S/N: 20030. Nominal capacity: 240 cpm. Maximum Container diameter: 4 in. (Cap Bowl diameter: 36 in. Cap size: 38mm x 12mm (1 1/2 in. dia. x 1/2 in. H.) caps. Maximum bottle size: 3 in. dia. x 6 in. H. Pneumacap Rotating Cap Sorter. General Electric Motor, 1/4 hp, 1725 rpm, 115/230 V, 5.0/2.5 amps, 60 Hz, single phase. Speed Selector Inc. Series 21 Fixed Center Drive, Model: 4C. Infeed/exit height: 3 ft. Overall dimensions: 8 ft. 7 in. L x 3 ft. 6 in. W x 7 ft. 7 in. H.





