

Stainless Steel Single Shell Insulated Tank- 270 Gallon

Mfg:

Model:

Stock No.: OI67

Serial No.:

Stainless Steel Single Shell Insulated Tank- 270 Gallon. Inside straight-wall dimensions: 4 ft. dia. x 2 ft. 11 in. H. Equipped with center bridge and flip top lids. Agitator dimensions: 2 ft.10 in. L x 2 in. W x 2 ft. 9 in. H. Baffle dimensions: 2 ft. 5 in. L x 6 in. W. Scraper dimensions: 16 in. L x 4 in. W. Reliance Electric Motor, 2 hp, 1140 rpm, 208-230/460 V, 6.4-6.4/3.2 amps, 60 Hz, 3 phase. Agitator Drive, final speed: 20 rpm. Inlets: (3) 2 in. S-Line fitting. Outlets: (1) 1-1/2 in. S-Line fitting. Overall dimensions: 4 ft. 3-1/2 in. L x 4 ft. 5 in. W x 6 ft. 11 in. H. This piece is being offered and sold as is. It may or may not leak or be complete. Please be sure and look at pictures and ask for additional pictures. Do not rely on original descriptions. MAKE US AN OFFER. NO REASONABLE OFFER WILL BE REFUSED.

