

Mission Centrifugal Pump

Mfg: Mission

Model:

Stock No.: OIP050

Serial No.: 75021-83-B

Mission Centrifugal Pump. S/N: 75021-83-B. Size: 3x1.5x10. Flow rate for new pump is 140 gpm with required horsepower and at 90 ft. TDH. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 10 in. Product contact areas are of 316 SS construction. Double mechanical seals with water flush. Reliance Electric Motor, 3 hp, 1755 rpm, 230/460 V, 7.6/3.8 amps, 60 Hz, 3 phase. Overall dimensions: 3 ft. 9 in. L x 1 ft. 2 in. W x 1 ft. 8 in. H. (ACN67a)

