

## Durco Centrifugal Pump

Mfg: Durco / Duriron

Model:

Stock No.: OIP083

Serial No.: 239665

Durco / Duriron Centrifugal Pump. S/N: 239665. Size: 1-1/2 x 1-6/60. Flow rate for new pump is 80 gpm with required horsepower. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Maximum design pressure: 275 psi @ 100 °F. Baldor motor: 1.5 hp, 2706 rpm, 230/460 V, 4.6/2.3 amps, 60 Hz, 3 phase. Inlets: 1-1/2 in. dia. 125 lb. ANSI flange. Outlets: 1 in. dia. 125 lb. ANSI flange. Materials of construction include 316 stainless steel. Overall dimensions: 2 ft. 11 in. L x 1 ft. 1/2 in. W x 1 ft. 3 in. H.(ACN17a).



