

Tri Clover PREDS Positive Displacement Pump

Mfg: Tri Clover

Model: PREDS125-R3M-UC4-ST-S

Stock No. OIP097.

Serial No. T2296J

Tri Clover PREDS Positive Displacement Pump. Model: PREDS125-R3M-UC4-ST-S. S/N: T2296J. Capacity: 79 gpm @ 80 psi. Maximum capacity: 120 gpm @ 20 psi. Displacement per 100 rpm: 30.0 gal. Seal option: double mechanical with flushing. Ajax Electric Motor, 7-1/2 hp, 1200 rpm, 230 rpm (final), 200 V, 22 amps, 60 Hz, 3 phase. Tri-Clover positive pumps handle high viscosity products at elevated GPM and pressure ratings, provide longer seal and rotor life, reduce maintenance costs and downtime, perform effectively on suction lift service, and handle liquids and semi-solids with entrained vapors. For operations such as: liquid sugar, tacky products like corn syrup, and viscous products. Inlets: (1) 9 in. L x 2-1/2 in. W rectangular infeed with a 15 in. L x 4 in. W flange and (4) 1/2 in. thru-holes. Outlets: (1) 3 in. dia. S-line fitting. Overall dimensions: 46 in. L x 20 in. W x 21 in. H.



