

Sihi Multi-Stage Liquid Pump

Mfg: SIHI

Model: AOHB3602 BN 001 01 0

Stock No.: PF8262.5

Serial No.: 2693465

Sihi Multi-Stage Liquid Pump. Model: AOHB3602 BN 001 01 0. S/N: 2693465. Maximum flow rate for new pump is 9 gpm with required horse power and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Self-priming. Maximum admissible pressure: 145 psi. Test pressure: 188 psi. Maximum admissible viscosity: 300 CST. Maximum speed: 1800 rpm. Baldor Motor, 5 hp, 1750 rpm, 208-230/460 V, 15.4-14.2/7.1 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 1-1/2 in. dia. ports with 2-bolt flanges. Overall dimensions: 3 ft. L x 1 ft. 3 in. W x 1 ft. 1 in. H.(ACN27a).



