

Gas Fired Tunnel Oven

Mfg:

Model:

Stock No: PMHT06

Serial No:

Gas Fired Tunnel Oven. (17) upper burners. Stainless steel construction. 8 ft. 11-1/2 in. oven section, fed by 36 in. L x 24 in. W product immersion section with 10 in. dia. drum leading to 5 in. oven input belt, 8 in. L out feed belt feeds second 36 in. L x 24 in. W product immersion section with 10 in. dia. drum, 18 in. and 72 in. out feed conveyors. Dayton electric fan driven air blow-offs. Grease trap catch basin. (4) stainless steel drip pans. 24 in. W stainless steel straight rod wire belt type conveyor with 1/2 in. gap between rods. U.S. Motors Unimount 125 1 HP motor. Chain drive. Square D Telemecanique model Altivar 16 motor control.

