

Waukesha 60 Positive Displacement Pump

Mfg: Waukesha


Model: 60

Stock No.: RBFM607.7

Serial No.:

Waukesha 60 Positive Displacement Pump. Model: 60. Flow rate for new pump is 80 gpm with required horsepower. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Features include: easy cleaning and disassembly, three-way mounting options, and non-galling, Waukesha "88" alloy rotors. Maximum pressure: 200 psi. Maximum speed: 600 rpm. Temperature range: -40°F to 300°F. Baldor Electric Motor, 5 hp, 1750 rpm, 208-230/460 V, 13.8-13.4/8.7 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 2-1/2 in. dia. S-line fittings. Overall dimensions: 4 ft. 8 in. L x 1 ft. 6 in. W x 1 ft. 8 in. H. (ACN102a).





0Y6R5G15E
J8X190Y8B8E1
3
208-250/460
13.8-15.4/3.7
1750
134TC 60
1-15 J 3
STL 3 73
100 485-C6NT
6200 1048
T000 001211000