

Waukesha 30 Positive Displacement Pump

Mfg: Waukesha

Model: 30

Stock No.: RBFM620B.15

Serial No.: 80875 SS

Waukesha 30 Positive Displacement Pump. Model: 30. S/N: 80875 SS. Flow rate for new pump is 36 gpm with required horsepower and pressure at 0 psi. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Features include: easy cleaning and disassembly, three-way mounting options, and non-galling, Waukesha "88" alloy rotors. Maximum pressure: 200 psi. Maximum speed: 600 rpm. Temperature range: -40°F to 300°F. 316 Stainless steel pump body, cover and shaft. Lesson Electric Motor, 5 hp, 1760 rpm, 208-230/460 V, 13/6.5 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 1-1/2 in. dia. S-line fittings. Overall dimensions: 3 ft. 8 in. L x 1 ft. 3 in. W x 1 ft. 7 in. H.(ACN88a).





