

Chester Jensen Plate Chiller

Mfg: Chester Jensen

Model: B-8-0T-736-60

Stock No: RBFM750AA.2a

Serial No: 7509

Chester Jensen Falling Film Plate Chiller. Model: B-8-0T-736-60. S/N: 7509. Refrigerant: polypropylene glycol. Number of plates: 8. Number of corrugations: 36. Total cooling surface area: 342 sq.ft. Plate dimensions: 5 ft. 2 in. L x 3 ft. 9 in. W. Collecting tank-180 Gallon. Inside straight wall dimensions: 5 ft. 4 in. L x 3 ft. 7 in. W x 1 ft. 3 in. H. Tri-Flo sanitary centrifugal pump. Model: C216MD181-S. S/N: 182852-02. Impeller diameter: 4-1/4 in. dia. Reliance electric motor, 5 hp, 3480 rpm, 230/460 V, 13.6/6.8 amps. Pump inlets: (1) 2-1/2 in. S-line fittings. Outlets: (1) 1-1/2 in. S-line fittings. Inlets: (1) 4 in. dia. port, (1) 2 in. dia. NPT fitting. Outlets: (1) 4 in. dia. port, (1) 2-1/2 in. dia. S-line fittings. Overall dimensions: 7 ft. 6 in. L x 4 ft. 4 in. W x 6 ft. 6 in. H.

Plate information:

Nat'l Bd No's: 4628, 4629, 4630, 4649, 4650, 4653, 4655, 4556.

S/N's: 29235, 29236, 29237, 29284, 29285, 29239, 29295, 29086.











