

Kinney Vacuum Pump

Mfg: Kinney

Model:

Stock No.: RBFM750N.

Serial No.:

Kinney Vacuum Pump. Motor, 3 hp, 1760 rpm, 200-230-460 V, 10-9/4.5 amps, 60 Hz, 3 phase. Inlets; (1) 2 in. dia. FNPT fitting (suction), (1) 1-1/2 in. dia. port (oil fill). Outlets: (1) 2 in. dia. FNPT fitting (discharge), (1) 1/2 in. dia. port (exhaust), (1) 1-1/2 in. dia. port (oil drain). Overall dimensions: 2 ft. 6 in. L x 11 in. W x 1 ft. 1/2 in. H.



