

Chester Jensen Falling Film Plate Chiller – 80 Tons

Mfg: Chester Jensen

Model:

Stock No: RBFM985.40

Serial No:

Chester Jensen Falling Film Plate Chiller. Cooling capacity: 80 tons at 128 gpm using full-flooded ammonia for a 26°F suction with a 15° TD. (4) plates with 36 corrugations each. Total cooling section area: 171 sq. ft. 200 psi @ 200 °F, shell thickness .045. Approximate reservoir tank capacity: 145 gallons. Inlets: (1) 1 in. MNPT (product), (1) 3 in. dia. pipe (ammonia). Outlets: (1) 3 in S-Line fitting, (1) in. MNPT (ammonia). Overall dimensions: 7 ft. 6 in. L x 4 ft. 1 in. W x 8 ft. 4 in. H.

Plate information:

Individual plate S/N(s): 27617, 27647, 27648, 27651. Corresponding National Board No(s). 3834, 3845, 3846, 3849.



