

Waukesha Cherry Burrell 6 Positive Displacement Pump

Mfg: Waukesha Cherry-Burrell

Model: 6

Stock No.: RBPM004

Serial No.: 150389

Waukesha Cherry Burrell 6 Positive Displacement Pump. Model: 6. S/N: 150389. Flow rate for new pump is 6 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Features include: easy cleaning and disassembly, three-way mounting options, and non-galling, Waukesha "88" alloy rotors. Seal option: double mechanical. 316 stainless steel product contact surface. Max psi: 200. Sew-Eurodrive motor, 1-1/2 hp, 1700 rpm, 230/460 V, 4.75/2.35 amps, 60 Hz, 3 phase. Sew-Eurodrive gear reducer, ratio: 3.15:1, rpm out: 540 (final). Inlets/outlets: (2) 1 in. dia. NPT fittings. Overall dimensions: 2 ft. 7 in. L x 1 ft. W x 1 ft. H. (ACN68a).



