

## Tri-Clover Positive Displacement Pump


Mfg: Tri-Clover

Model: PR125-3-UC4-ST-S

Stock No: RCJF1632D

Serial No: X0510

Tri-Clover Positive Displacement Pump. Model: PR125-3-UC4-ST-S. S/N: X0510. Flow rate for new pump is 120 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Baldor Electric motor: 10 Hp, 1760 Rpm, 208-230/460 V, 28.5-28.4/14.2 A, 60 Hz, 3 Phase. APG drive: 20.0 Input Hp, 6.2 ratio, 4289 torque. Overall dimensions: 5 ft. L x 2 ft. W x 5 ft. 2-1/8 in. H.





**BALDOR®**  
INDUSTRIAL MOTOR

CAT. NO.	CM3714T		
SPEC.	37G814Y660H1		
HP	10		
VOLTS	208-230/460		
AMPS	28.5-28.4/14.2		
R.P.M.	1760		
FRAME	215TC	HZ 60	PH 3
SER. F.	1.15	CODE J	DES B CLASS F
NEMA NOM. EFF.	89.5	%	P.F. 73
RATING	40C AMB-CONT.		
CC	010A	USABLE AT 208V	28.5 A
BEARINGS	DE 6307	ODE 6206	
ENCL	TEFC EN F0502090610		

MADE BY BALDOR ELECTRIC CO. U.S.A.

