

### Waukesha 220 Positive Displacement Pump

**Mfg: Waukesha Cherry-Burrell**

**Model: 220**

**Stock No.: RCSC1352.90**

**Serial No.: 309190-02**

SPX Waukesha Cherry-Burrell Positive Displacement Pump. Model: 220. S/N: 309190-02. Also marked serial: 02-75696. 3A Sanitary. Universal I series. Flow rate for new pump is 310 gpm with required horsepower and RPM. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Displacement per revolution: 0.522 gallon. Maximum pressure: 200 PSI. Estimated flow rate with this gear drive is 36 GPM. SEW-Eurodrive gear drive ratio: 25.23 (final RPM 69). Baldor Motor: 5 HP, 208-230/460V, 13.9-13.4/6.7 amps, 1750 RPM, 60 Hz, 3-phase. Inlet/outlet ports: 4 in. dia I-line fittings. Overall dimensions: 4 ft. 9 in. L x 1 ft. 6 in. W x 1 ft. 10 in. H. (ACN208-265)







