

Vilter VMC 440 8-Cylinder Reciprocating Compressor - 40 HP

Mfg: Vilter

Model: 448

Stock No.: RFOK01

Serial No.: R14422

Vilter VMC 440-Series Reciprocating Compressor. Model: 448. Number of cylinders: 8. Serial: R14422. Size: AB448B. Order No.: F98802. Refrigerant: AMMO (ammonia). Displacement: 182 CFM. Nominal ratings: 94 TR at +20F / +95F (R-22 freon); 93 TR at +20F / +95F (R-717 ammonia). Lincoln Motor: 40 HP, 1748 RPM, 230/460V, 96/48 amps, 3-phase, 60 Hz, frame 364-U. Compressor weight: 3400 lbs. Ports (suction/discharge): 4 in. / 3 in. Previously used with ammonia refrigerant. Ports have been capped and unit will be stored indoors.



