

Vilter VMC 440 4-Cylinder Reciprocating Compressor - 50 HP

Mfg: Vilter

Model: 444

Stock No.: RFOK05

Serial No.: 12541 A RC

Vilter VMC 440-Series Reciprocating Compressor. Model: VMC 440 series. Serial: 12541 A RC. Order: C59210. Size: 444. Voltage: 230. Refrigerant: AMMO (R-717 ammonia). Number of cylinders: 4. Nominal rating (+20F / +95F): 56.8 TR (R717 Ammonia. Displacement: 155 M3hr (91.23 CFM). Lincoln motor: 50 HP, 1745 RPM, 230/460V, 119/59.5 amps, 60 Hz, 3-phase, 365U frame. Ports (in/out): 3 in./ 2.5 in. Compressor weight: 2,700 lbs. Motor: 50 HP. Previously run with ammonia refrigerant. Ports have been capped and unit is stored indoors.

