

Urschel Slicer, Model O

Mfg: Urschel

Model: O

Stock No. RFPM268.12a

Serial No. _____

Urschel Slicer. Model: O. (15) Cutting blades: 3 in. L x 1 in. W. Cutting/slicing wheel: 15 in. diameter. Baldor Industrial Motor (blades), 2 hp, 1725 rpm, 208-220/440 V, 3.4-3.2/1.6 amps, 60 Hz, 3 phase. General Electric Motor (belt), 3/4 hp, 1720 rpm, 208-220/440 V, 3.7-3.5/1.7 amps, 60 Hz, 3 phase. The Urschel Model O specializes in crosscut bias slicing of elongated products including: pickles, carrots, celery, rhubarb, okra, potatoes, squash, etc. The machine features a wide selection of slice thicknesses, continuous operation for uninterrupted production, and simplified design for easy cleanup and maintenance. (2) Motor disconnect switches. (4) casters for easy positioning. Product inlet: 40 in. L x 3 in. W. Outlet: 3 in. W x 3 in. H. Overall dimensions: 10 ft. 2 in. L x 33 in. W x 64 in. H.



