

## Votator Scrape Surface Heat Exchanger 3 x12

Mfg: **Votator**

Model: **XTW**

Stock No. **RFBM324.2a**

Serial No. **7709**

Votator Scrape Surface Heat Exchanger 3x12. Model: XTW. S/N: 7709. 316 stainless steel. Chamber dimensions: 3 in. diameter x 12 in. L. Concentric shaft: 2-1/4 in. diameter x 12 in. L. (2) Bakelite scrapers: 12 in L x 1 in. W. Motor, 2 hp, 1800 rpm, 60 cycles, 3 phase. Lima Electric 4-Speed Gear Drive. Inlets: (1) 3/4 in. dia. NPT (female, jacket), (1) 3/4 in. NPT (female, product). Outlets: (1) 3/4 in. dia. NPT (female, jacket), (1) 3/4 in. dia. NPT (female). Overall dimensions: 52 in. L x 15 in. W x 25 in. H.



