

Hoffman Multi-Stage Centrifugal Blower/Exhauster

Mfg: Hoffman

Model: 76104A

Stock No. RFPM451.

Serial No. 0688033

Hoffman Multi-Stage Centrifugal Blower/Exhauster. Model: 76104A. S/N: 0688033. Number of stages: 7. Impeller diameter: 26 in. Approximate blower performance @ 8000 cfm inlet airflow (discharge pressure): 13 psig. Approximate exhauster performance @ 8000 cfm inlet airflow (vacuum): 14 in. Hg. Toshiba Motor, 125 hp, 3550 rpm, 230/460 V, 294/147 amps, 60 Hz, 3 phase. Universal Silencer, Model CCF-14, S/N: R2854-87). With its unsurpassed durability and efficient operation, Hoffman blowers/exhausters are the preferred choice for aeration, combustion, and vacuum service, etc. Sample applications: aquaculture, cement and lime, chemical, coal bed/landfill, electronics, oil and gas, power generations, process gas, pulp and paper, refining, resin and plastic, soil remediation, and wastewater. Inlets: (1) 23 in. dia. suction port. Outlets: (1) 14 in. dia. discharge with a 21 in. dia. flange and (8) 3/4 in. dia. thru-holes at center distances of 5 in. Overall dimensions: 10 in. L x 41 in. W x 77 in. H.

