

Votator Stainless Steel Scrape Surface Heat Exchanger 3 x 12

Mfg: **Votator**

Model: **X1D**

Stock No. **RFPM479.1**

Serial No. **66710**

Votator Stainless Steel Scrape Surface Heat Exchanger 3x12. Model: X1D. S/N: 66710. Tube chamber dimensions: 3 in. diameter x 12 in. L. Concentric shaft: 1-3/4 in. diameter x 12 in. L. (2) Bakelite scrapers: 12 in. L x 1 in. W. U.S. Motor, 2 hp, 1800 rpm, 230/460 V, 7.2/3.6 amps, 60 cycles. U.S. Varidrive Module, maximum speed: 1030 rpm, minimum speed: 103 rpm. Inlets: (1) 3/4 in. dia. NPT (female, jacket), (1) 1 in. diameter threaded (male). Outlets: (1) 3/4 in. dia. NPT (female, jacket), (1) 3/4 in. diameter threaded (female). Overall dimensions: 55 in. L x 18 in. W x 40 in. H.



