

Votator Scrape Surface Heat Exchanger 3 x 12

Mfg: **Votator**

Model: **X1-W**

Stock No. **RFPM480.1**

Serial No. **62383**

Votator Scrape Surface Heat Exchanger 3 x 12. Model: X1-W. S/N: 62383. Chamber dimensions: 3 in. diameter x 12 in. L. Scraper shaft: 2-1/4 in. diameter x 11-3/4 in. L. (2) 11-3/4 in L x 1 in. W bakelite scrapers. U.S. Varidrive Speed Motor, 2 hp, 1200 rpm, 220/440 V, 8.5/4.25 amps, 60 cycles, 3 phase, maximum speed: 1170 rpm, minimum speed: 242 rpm. Product inlet: (1) 3/4 in. threaded (male, jacket), 1-1/2 in. threaded (male). Product outlet: (1) 3/4 in. threaded (male, jacket), (1) 1-1/2 threaded (male). Overall dimensions: 52 in. L x 24 in. W x 36 in. H.



