

## Chester Jensen Falling Film Plate Chiller – 80 Tons

Mfg: Chester Jensen

Model: B-4-OT-4-32

Stock No: RGMB163.10

Serial No: 9087-P

Chester Jensen Falling Film Plate Chiller. Model: B-4-OT-4-32. S/N: 9087-P. Cooling capacity: 80 tons at 128 gpm for a 26°F suction using full-flooded ammonia with a 15° TD. (4) plates with 32 corrugations each. Total cooling section area: 171 sq. ft. Plate dimensions: 5 ft. L x 3 ft. 9 in. H. Collection tank: 125 Gallon, inside straight-wall dimensions: 5 ft. 5 in. L x 2 ft. 4 in. W x 1 ft. 4 in. H. Inlet/Outlets: (3) 2 in. dia. ports, (1) 1- 1/2 in. dia. port, (1) 1 in. dia. port. Overall dimensions: 8 ft. 10 in. L x 4 ft. W x 8 ft. H.





