

Aurora Centrifugal Pump

Mfg: Aurora



Model:

Stock No: RGMP281B

Serial No: 02-450298

Aurora Centrifugal Pump. S/N: 02-450298. Type: 341A BF. Size: 5x6x11. Flow rate for new pump is 1,100 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Marathon electric motor, 15-1/2 hp, 1745/1455 rpm, 208-230/460-190/380 V, 43-39.2/19.6-37.6/18.8 FLA, 60/50 Hz, 3 phase. Inlet: (1) 6 in. dia. flanged port. Outlet: (1) 5 in. dia. flanged port. Overall dimensions: 2 ft. 3 in. L x 1 ft. 10-1/2 in. W x 1 ft. 7-1/2 in. H.





MARATHON ELECTRIC
WAUSAU, WISCONSIN 54401

CAT NO- M329 HZ-60 50
 MODEL- 9VC254TTDX7044AB L HP- 15 12
 FR-254JM PH-3 TYPE-TDR RPM-1745 1455
 AMB- 40°C INS-B₂ DUTY-CONT. VOLT- 208-230/460 190/380
 DES-B FLA- 43-39.2/19.6 37.6/18.8
 SF- 1.15 1.15
 SFA-
 CODE-G ENC-DP
 1.0 S.F. @ 208 VOLTS.
 PE BRG- 309 OPE BRG- 208

FLEF 87.5 FLPF 81.3
 LOW VOLTAGE HIGH VOLTAGE
 T4 T5 T6 T4 T5 T6
 T7 T8 T9 T7 T8 T9
 T1 T2 T3 T1 T2 T3
 LINE LINE LINE LINE LINE LINE

WARNING: FAILURE TO FOLLOW ALL SAFETY INFORMATION CAN RESULT IN SERIOUS PERSONAL INJURY OR DEATH. DISCONNECT ALL POWER BEFORE SERVICING. INSTALL AND GROUND PER LOCAL AND NATIONAL CODES. CONSULT QUALIFIED PERSONNEL WITH ANY QUESTIONS.

WISIN 54401

HZ-60 50
 HP- 15 12
 RPM-1745 1455
 VOLT- 208-230/460 190/380
 FLA- 43-39.2/19.6 37.6/18.8
 SF- 1.15 1.15
 SFA-
 CODE-G ENC-DP
 1.0 S.F. @ 208 VOLTS.
 PE BRG- 309 OPE BRG- 208

T6
 T9
 T3
 LINE
 193914

FIP
 UL

OLLOW ALL SAFETY INFORMATION CAN RESULT IN