

**Bell & Gossett 1510 Series Centrifugal Pump - 35 gpm**

**Mfg: Bell & Gossett**

**Model: 11/4BC-75/8-BF**

**Stock No.: RGMP404E**

**Serial No.: 1203461**

Bell & Gossett 1510 Series Centrifugal Pump. Model: 11/4BC-75/8-BF. S/N: 1203461. Ident. No: M38. Capacity: 35 gpm @ 60 tdh. Impeller diameter: 7-1/2 in. Maximum working pressure: 175 psi. Inlets: (1) 1-1/2 in. dia. flanged port. Outlets: (1) 1-1/4 in. dia. flanged port. Overall dimensions: 2 ft. 7 in. L x 1 ft. 3 in. W x 2 ft. 3 in. H.





