

## 1995 Kice Industries Inc. Vertical Dust Collector

Mfg: Kice Industries Inc.

Model: HRB 12-6

Stock No: RGMP407.3a

Serial No: 131472

1995 Kice Industries Inc. Vertical Dust Collector. Model: HRB 12-6. S/N: 131472. Number of filters: 12. Filter dimensions: 4 in. dia. x 5 ft. 9 in. H. Total filter surface area: 85 sq. ft. Filter access door dimensions: 1 ft. 3 in. W x 3 ft. 5 in. H. Reliance Electric motor, 1/3 hp, 1725 rpm, 208-230/460 V, 1.8-1.6/0.8 amps, 60 Hz. right angle drive. Kice Industries VJ round airlock, Model: VJ 8x6x6, S/N: 131472 C19909. Reliance Electric motor, 1/2 hp, 1725 rpm, 208-230/460-480 V, 60 Hz, 3 phase. SM-Cyclo Sumitomo drive, ratio 29:1, final speed: 59.4 rpm, torque: 599 in. lbs. Asco Tri-Point pressure operated switch, S/N: A276657, Cat. No: SA310. Asco Tri-Point pressure transducer, S/N: A254227, Cat. No: TA31A11, fluid: air, fluid: fuel gas, range: 0-27 in. W.C., maximum pressure: 15 psig. Applications include removing dust and other product streams from processing operations. Inlets: (1) 4 in. dia. port, (2) 3 in. dia. ports. Outlets: (1) 5-1/2 in. L x 5-1/2 in. W discharge. Overall dimensions: 4 ft. L x 3 ft. 6-1/4 in. W x 12 ft. 7-1/2 in. H.(ACN117a).











