

New Motors

Mfg:

Model:

Stock No. RLOL384.3

Serial No.

Leeson Motor, Model C6T17VC6E, 1/3 hp, 1,725 rpm, 208-230/460 volt, 1.3-1.3/0.65 amps, 60 Hz, 3 phase, Frame: B56C.



Baldor Motor, 1-1/2 hp, 3,450 rpm, 208-230/460 volt, 4.9-4.6/2.3 amps, 60 Hz, 3 phase. Frame 56C, Cat: CM3550.



Baldor Motor, 1/3 Hp, 1,710 rpm, 208-230/460 volt, 1.4-1.3/0.70 amps, 60 Hz, 3 phase. Built In Gear Reduction: Ratio 30, Torque: 320 in. lbs. Final rpm: 57.



(2 motors): Reliance Motor: 3/4 hp, 1,725 rpm, 208-230/460 volt, 2.9-2.6/1.3 amps, 60 Hz, 3 phase. Frame: ED56C, ID: P56H1319Z.



(2 motors): Reliance Motor: 1/2 hp, 1,725 rpm, 208-230/460 volt, 2.2-2.2/1.1 amps, 60 Hz, 3 phase. frame FB56C. ID Numbers: P56H1320Z, P56H1320G.



GE Motors, Motor: Model 5HK32FN3123, 1/4 Hp, 1,725 rpm, 115 volt, 5.1 amps, 60 Hz, 1 phase. Frame 48.

