

## Remanufactured Pacemaker Motor- 15/10/7.5/5 HP

Mfg: Pacemaker

Model: 1138630001

Stock No. RPAG1123.1

Serial No.

Remanufactured Pacemaker Motor- 15/10/7.5/5 HP. Model: 1138630001. Explosion proof. Motor specifications: 15/10/7.5/5 hp, 1765/1160/875/580 rpm, 460 V, 18.5/13.3/14.6/13.4 amps, 60 Hz, 3 phase. Type: CEE5NB. Frame: 324T. Code: H. UL Listed No: AJ42663. Class I Group C & D. Shaft diameter: 2-1/8 in. Overall dimensions: 30 in. L x 19 in. W x 17 in. H.

