

Reliance Electric E-Master Duty Master A-C Motor- 1 HP

Mfg: Reliance

Model:

Stock No. RPAG1124Q.

Serial No.:

Reliance Electric E-Master Duty Master A-C Motor- 1 HP. ID: P14X3967N-DC. Explosion proof. Motor specifications: 1 hp, 1725 rpm, 230/460 V, 2.8-1.4 amps, 60 Hz, 3 phase. Frame: HD143T. Type: P. Insulation class: F. Design: B. Code: J. UL Listed No: SAF114144. Class I Group D. Class II Groups F & G. Shaft diameter: 7/8 in. Overall dimensions: 15-1/2 in. L x 12 in. W x 8 in. H.

