

Mycom 6-Cylinder Reciprocating Compressor Parts Machine

Mfg: Mycom

Model: 6J2

Stock No: RPCN202a.2a

Serial No: 11759

Mycom 6-Cylinder Reciprocating Compressor Parts Machine. Model: 6J2. S/N: 11759. Capabilities of the 6J compressor: 74.9 TR at 72.9 BHP using R-22 with a 40°F Suction, 105°F Discharge, 15°F Superheat, and 0°F Subcooling at a max rpm of 1450. Displacement: 165 cfm. These items are sold as parts for a compressor package and the unit was set up for Freon, R-12, R-22, R-404, and R-502. Parts / items include: compressor minus pistons and piston sleeves, a 50 hp electric motor, and a Howe recirculator. Connections: 3 in. suction and 2-1/2 in. discharge.(ACN182a-BC/Motor).

