

APV Positive Displacement Pump

Mfg: APV

Model: 6R+BS

Stock No: SCJC152.7

Serial No: P-6755-0997

APV Positive Displacement Pump. Model: 6R+BS. S/N: P-6755-0997. Flow rate for new pump is 260 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. U.S. Electrical Motors Co. 5 hp, 1750 rpm, 208-230/460 v, 14.2-12.8/6.4 a, 60 Hz, 3 phase. Dodge APG drive: 10 in hp, 230.26 out rpm, 2630 torque, 7.600 ratio. (2) 5-5/8 in. rubber lobe rotors. Stainless steel base mounted. Inlet/outlet: (2) 3 in. S-line. Overall dimensions: 4 ft. 4 in. L x 1 ft. 10 in. W x 2 ft. 1 in. H.





