

Vanmark 2700-Series Peeler / Washer

Mfg: Vanmark

Model: 2745

Stock No: SFEP029.8

Serial No:

Vanmark 2700-Series Peeler / Washer. Model: 2745. Stainless steel construction. Unit has the (8) Char-Lynn hydraulic motors which are designed to rotate the rollers. Unit is equipped with a tumbling unit that has (10) paddle shafts that extend the inner length of washer. Paddle dimensions: 8 in. L x 4 in. W. Manual discharge gate. Control box that has a principal on/off switch, emergency stop switch, and (4) start/stop motor switches. This machine is designed for peeling, washing, and/or scrubbing root crops, vegetables and fruits. Hydraulic oil reservoir: 15 Gallon. Baldor electric motor, 20 hp, 1760 rpm, 230/460 V, 48/24 amps, 60 Hz, 3 phase. Washer inlet: 2 ft. L x 1 ft. 3 in. W. Outlet: (1) 4 in. dia. pipe (water), (1) 1 ft. 6 in. W x 8 in. L discharge chute at a height of 4 ft. Approximate weight: 2,200 lbs. Overall dimensions: 11 ft. 3 in. L x 4 ft. 3-½ in. W x 6 ft. H.







