

Mycom 6-Cylinder Reciprocating Compressor – 60 HP

Mfg: Mycom Cimco

Model: 6J

Stock No: SFEP1232.11a

Serial No: 12024

Mycom 6J 6-Cylinder Reciprocating Compressor. Model: 6J. S/N: 12024. Refrigerant: This unit is set up for Freon, R-12, R-22, R-404, R-502. Displacement: 165 cfm. Maximum speed: 1,450 rpm. Bore: 3-3/4 in. Stroke: 3 in. General Electric motor, 60 hp, 1780 rpm, 976.12 rpm (final), 230/460V, 149.8-74.9 amps, 60 Hz, 3 phase. Inlets: (1) 3 in. dia. suction pipe. Outlets: (1) 2-1/2 in. dia. discharge port. Overall dimensions: 7 ft. 10 in. L x 3 ft. 7 in. W x 4 ft. 4 in. H. (ACN175-BC/Motor)







