

## APV Crepaco R-Series Positive Displacement Pump

Mfg: APV Crepaco

Model: R1R

Stock No: SFF446.1a

Serial No: 20086

APV Crepaco R-Series Positive Displacement Pump. Model: R1R. S/N: 20086. Capacity: 3.5 gpm. Displacement per Revolution: 0.01 gal. Maximum speed: 600 rpm. Reliance Electric Motor, 1.5 hp, 1750 rpm, 180 V (armature)-100/200 V (field), 7.4 amps (armature)-0.96/0.48 amps (field). Right Angle Motor Drive, 5 ratio, 350 rpm (final). Inlets/outlets: (2) 1-1/2 in. dia. ACME fittings. Overall dimensions: 3 ft. 8 in. L x 2 ft. 10in. W x 1 ft. 5 in. H.



