

APV Heated Coating Drum

Mfg: APV

Model:

Stock No: SGM4035.45

Serial No: 233/1

APV Heated Coating Drum. Machine No: 233/1. Contract No: SCF965016. Inside straight-wall dimensions: 3 ft. 3 in. dia. x 13 ft. 4 in. L. Sew-Eurodrive Motor and Variable Speed Reducer, 3 hp, 70/353 rpm (final), 266/460 V, 7.63/4.44 amps, 60 Hz, 3 phase, ratio: 12.39. Eclipse Dungs Ignition Transformer, primary voltage: 120 V, 1.5 amps, 60 Hz, secondary voltage: 6000 V, 0.02 amps. (1) 1 ft. 1 ¾ in. W x 1 ft 7 ½ in. H. access door. Inlets: (1) 1 ½ in. dia. FNPT fuel feed port, (1) 1 ft. 11-1/2 in. dia. product infeed port, (1) 5 ¾ in. dia. port. Outlets: (1) 2 ½ in. dia. drain port, (1) 6 in. dia. flanged vent port, (1) 1 ft. 11 in. L x 1 ft. W product discharge port. Overall dimensions: 16 ft. 9 in. L x 6 ft. 2 in. W x 13 ft. H. (BH).









