

## Food Additive Skid – 12 Gallons


**Mfg:**


**Model:**

**Stock No: SGMN215.20**

**Serial No:**

Food Additive Skid. Tank capacity: 12 gallons. Usable dimensions: 18 in. H x 14-1/4 in. diameter. Includes strainer basket that holds approximately 3.5 gallons of product. Basket has 1/8 in. holes. Baldor Electric motor: serial no. 119-93. cat. No. CDPWD3330. 1/2 hp, 1750 rpm, 4.8 amps. Sew Eurodrive, Inc. Type: R40LP. S.O. 8500444243. Skid includes: Micro Motion DS012S100SU flow sensor, Daniel Controls pressure dial gauge and (4) rolling castors for ease of mobility. (1) 1/2 in. outlet and (1) 1 in. outlet. Overall dimensions: 3 ft. 11 in. L x 2 ft. 1 in. W x 4 ft. 2 in. H.





INST. NO.	7DPWD3330		
SPEC.	33-21422122		
H.P.	1/2	ENCL	TELY
R.P.M.	1750	SER #	115-33
FRAME	56C	TYPE	PK3335R
ARM	08	AMPS	4.0
VOLTS			
FIELD			
INSUL.	F	AMB.	133
COU	CONT	SUPPLY	F. 3.3
BRG/DE	3203	BRG/ODE	5203
BRUSH	PP5011T01		

