

**2001 Goedhart Cooling Equipment Stainless Steel Evaporator Coils – 10 tons**



**Mfg: Goedhart Cooling Equipment**


**Model:**

**Stock No: SGMPB057B**

**Serial No:**

(3) 2001 Goedhart Cooling Equipment Stainless Steel Evaporator Coils. Approximate capacity: 10 TR each. Manufacture no: 01-6791-010. Type: Advantec 1400-1800S. Client refr: 371535. Medium: NH3. Tube volume: 220 dm<sup>3</sup>. Mass (empty): 660 kg. Min. Working temp: -55 °C. Max Working temp: 55 °C. Test pressure: 30 Bar. Max working pressure: 24 Bar. Each coil has (156) ¾ in. tubes at 4 fins per inch. These coils were originally setup to be used with glycol refrigerant in a Frigoscandia impingement chiller. Each has been successfully leak checked. Quantity available: 3. Overall dimensions: 175 in. L x 46 in. W x 32 in. H.





Material		Min. Working Temp.		Goedhart	
Fluid in pipe	2001	Min. Working Temp.	-75 °C	Order No.	100-1000000
Medium	1.43	Max. Working Temp.	55 °C	Order No.	100-1000000
Tube length	2500	Wall thickness	30	Order No.	100-1000000
Tube weight	1500	Max. Working pressure	2.4	Order No.	100-1000000