

APV Positive Displacement Pump

Mfg: APV

Model: R4RIHD

Stock No: SIBI147G.10

Serial No: PP-2401-0699

APV Positive Displacement Pump. Model: R4RIHD. S/N: PP-2401-0699. Flow rate for new pump is 160 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Motor drive 35. 5:1 ratio, 1750 rpm in, 8998 torque. U. S. Electrical Motors 7.5 hp, 1745 rpm, 208-230/460 volts, 25.0/12.5 amps, 60 Hz, 3 phase. (2) Rotors included in pump. Inlets: (1) 4 in. s-line, (2) 2 in. s-line. Outlet: (1) 3 in. s-line. Overall dimensions: 4 ft. 10 ½ in. L. x 1 ft. 10 ¼ in. W. x 1 ft. 11 ½ in. H.



