

1990 Viatec™ Perma-San® Stainless Steel Jacketed Tank with Agitator – 30 Gallons

Mfg: Viatec™

Model: 30 Gallon JOVS

Stock No: SIBI221.2

Serial No: 53022-1

1990 Viatec™ Perma-San® Stainless Steel Jacketed Tank. Model: 30 Gallon JOVS. S/N: 53022-1. National Bd no: 5960. Approximate capacity: 30 gallons. Inside tank dimensions: 1 ft. 6 in. dia. x 2 ft. 4 in. straight wall. Certified by Will / Flow Corp. Tank material of construction: stainless steel, inside 316 grade. Shell thickness: .161 in. Head thickness: .159 in. MAWP jacket: 130 PSI at 360°F. MDMT jacket: 130 PSI at -20°F. Reliance Electric Company motor: ID no. T56H1019R-YQ, ¼ HP, 1725 RPM, ARM Volts: 90, ARM Amps: 2.8. Boston Gear drive: .750 Hp, 1750 input rpm, 106 output torque. Perma-San® Agitator. Model no. TGPF-25. (1) 7 in. dia. impeller. Inlets/outlets: (2) ¾ in. MNPT. (1) ¾ in. FNPT. (2) ½ in. MNPT. Overall dimensions: 2 ft. L x 2 ft. W x 6 ft. 3 in. H.







