

Waukesha Model 30 Positive Displacement Pump on Cart

Mfg: Waukesha

Model: 030

Stock No.: SIKH328

Serial No.: 9784 SS

Waukesha Displacement Pump. Model: 030. Serial: 9784SS. Displacement per revolution: 0.060 gallons (0.227 liters). Nominal capacity: 36 GPM (8.2 m³/hr). Maximum pressure: 200 PSI (13.8 bar). Speed range: 0-600 RPM. Temperature range: -40F to 300 F (-40C to 149C). Weight: 130 lbs. Port size: 1.5 in. Reeves Varidrive: 1 HP, 208-230/460V, 60 Hz, 3-phase. Overall dimensions: 8.5 in. W x 14.58 in. L x 10.29 in. H.





