

Tri Clover PRS60 Positive Displacement Pump

Mfg: Tri Clover

Model: PRS60-3M-UH2-ST-S

Stock No. SKFC004.a

Serial No. 112929-01

Tri Clover PRS60 Positive Displacement Pump. Model: PRS60-3M-UH2-ST-S. S/N: 112929-01. Maximum capacity @ 20 psi: 60 gpm. Displacement per 100 revolutions: 17.5 gal. Side-mount. Tri Clover pumps perform more effective on suction lift service; handle anything from liquids to semi-solids with entrained vapors. Reduced maintenance costs and downtime with their longer seal and rotor life. Inlets/outlets: (2) 3 in. dia. S-Line fittings. Overall dimensions: 1 ft. 5 in. L x 1 ft. 3 in. W x 1 ft. 4 in. H.



