

Pacific 9 Head Rotary Pressure Filler

Mfg: Pacific

Model:

Stock No. SKFC027.45

Serial No. 1115

Pacific 9 Head Rotary Pressure Filler. S/N: 1115. Previous duty: filling mayonnaise @ 40-50 bpm. Distance between valves: 8-1/4 in. Maximum bottle size: 6 in. dia. x 11 in. H. 18 in. L timing screw. (2) Waukesha 130 Positive Displacement Pumps, Model: 130, S/N's: 20481597 and 101308 SS. Displacement per revolution: 0.254 gal. Nominal capacity: 150 gpm. Features include: bi-directional flow, large diameter shafts for greater strength & stiffness, rotor/shaft connection sealed from the product zone, extended-life outer seal, mechanical seals standard, standard 316 pump body, exclusive, non-galling Waukesha "88" alloy rotors for tighter running clearances and higher efficiencies. Reliance Electric Motor, 5 hp, 1730 rpm, 460 V, 6.1 amps, 60 Hz, 3 phase. Inlets: 2 in. dia. S-line fittings. Overall dimensions: 89 in. L x 55 in. W x 88-1/2 in. H. 1994 Oakes and Burger Control Panel, Model: 884, Dwg: 879, electrical requirements: 120 V, single phase.









