

Goulds Centrifugal Pump



Mfg: Goulds


Model:

Stock No: SMBV006

Serial No:

Goulds Centrifugal Pump. General Electric motor: 5 hp, 3450 rpm, 230/460 volts, 12.6/6.3 amps, 60 HZ, 3 phase. Inlets: (1) 1-1/2 in. diameter flange. 4 mounting holes with 5/8 in. dia. Adjacent are 2-3/4 in. and opposite 3-3/4 in. Outlets: (1) 1 in. diameter flange. 4 mounting holes with 5/8 in. dia. Adjacent are 2-1/4 in. and opposite 3-1/4 in. Overall dimensions: 3 ft. 2-3/4 in. L. x 1 ft. 2 in. W. x 1 ft. 3-1/4 in. H.





MODEL 3K184S0103	STK NO. K548
HP 3	SF 1.15 RATING CONT
VOLTS 230/460	PHASE 3 HERTZ 60
AMP 12.6 / 6.3	RPM 3450 NEW EFF. 81.5
WINDING F DEG. MAX. AVE. 40	CONNECTION
FRAME 184T	SEMA B
ENCL. TE TYPE K CODE J	
SHAFT END 6306ZZ	
FRS 6306ZZ	▲▲▲▲
SER. NO. 3550020003	230V LINE 460V LINE
USABLE ON 200V NETWORKS AT 14 AMP	




FORM W410-B SEVERE DUTY MOTOR MADE IN TAIWAN