

## 1998 Viking Positive Displacement Pump

Mfg: Viking

Model: G32

Stock No.: SNBB520

Serial No.: 10978179

1998 Viking Positive Displacement Pump. Model: G32, S/N: 10978179. Nominal capacity: 6 gpm. Internal gear pump with single mechanical seals. Reliance Electric Motor, 1 hp, 1140 rpm, 230/460 V, 3.4/1.7 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 1 in. dia. MPT. The G32 is packed seal pump that utilizes a simple and economical "floating rotor" design, in which the rotor/shaft is not retained by a thrust bearing, and is allowed to "float" within the pump head which reduces the available pressure and allowable viscosity. Overall dimensions: 29 in. L x 12 in. W x 10 in. H.

