

General Conveyor Co. Stainless Steel Table Top Conveyor

Mfg: General Conveyor Co.

Model:

Stock No. SNCC605F.

Serial No.:

General Conveyor Co. Stainless Steel Table Top Conveyor. 6 in. D X 3/4 in W sprocket with 1-1/2 in. teeth spacing. Eurodrive Motor: 0.44-.75 Hp, 2250 to 2450 rpm, 60 Hz. Eurodrive gear box ratio: 25.7. Adjustable guide rails. Max product size: 3-1/4. Infeed/outfeed height: 34 in. Overall Dimensions: 48 in. L x 19-1/2 in. W x 39-1/2 H.

