

ARO Air Operated Pump

Mfg: ARO

Model: 630408

Stock No. SNPM014.3

Serial No.

ARO Air Operated Pump. Model: 630408. 2-Ball style air pump designed to transfer medium viscosity fluids; typically in the range of 1,000 to 20,000 centipoise. Air inlet pressure range: 30-120 psi (2-8.3 bar). Fluid pressure range: 270-1350 psi (18.3-91.8 bar). Max. recorded cycles per minute: 60. Displacement per cycle: 11 cu in. (180.2 cu cm). Cycles per gallon (liter): 21 (5.5). Flow @ 60 cycles/min: 2.8 gpm (10.5 lpm). Inlets: (1) 1-1/2 in. dia. suction tube. Outlets: (1) 1/2 in. ball valve. Overall dimensions: 10 in. L x 7 in. W x 32-1/2 in. H.

