

Odenberg Can Unscrambler Bed

Mfg: Odenberg

Model:

Stock No. SNPM035.3a

Serial No.

Odenberg Can Unscrambler Bed. Maximum aperture/clearance above belts: 5 ½ in. W x 2 ½ in. H. Number of channels: 8. Peg diameter: 3/8 in. Chain pitch: 5 in. The Odenberg Unscrambler Bed gently brings cans out of the cooling canal to be placed on a cross-conveyer for further processing. Inlets: (1) 29 ½ in. L x 19 ½ in. W access door. Outlets: (1) 3 in. dia. port with a 7 ½ in. dia. flange and (4) ¾ holes at a center-to-center distance of 4 ¼, (1) 4 in. bypass valve NPT (female). Overall dimensions: 11 ft. 2 in. L x 5 ft. 5 in. W x 7 ft. H.



