

## Viking Universal Seal Rotary Pump

Mfg: Viking

Model: H124

Stock No.: SNSL264.1

Serial No.: 0814478

Viking Universal Seal Rotary Pump. Model: H124. S/N: 0814478. Nominal capacity: 15 gpm. General Electric Motor, 1/2 hp, 1725 rpm, 208/460 V, 2.3-2.2/1.1 amps, 60 Hz, 3 phase. The Viking's "gear-within-gear" pumping principle provides low-shear, nonpulsating, cushioned pumping for a wide range of applications without foaming or churning. The enlarged bearing housing at the rear of the pump provides easy drive-end access, and accepts various sealing options including: packing, component mechanical seals, cartridge single-mechanical seals, cartridge double-mechanical seals, and cartridge triple-lip seals. Pump inlet: 2 in. threaded (female). Outlet: 2 in. threaded (female). Overall dimensions: 20 in. L x 18 in. W x 13 in. H. (ACN12a).



