

Foster Rotary Vane Pump

Mfg: Foster

Model: RIF3-3

Stock No. SNSL270.2

Serial No. 73248

Foster Rotary Vane Pump. Model: RIF3-3. S/N: 73248. Capacity: 20 gpm @ 150,000 SSU. Reliance Electric motor: 3 hp, 1740 rpm, 230/460 V, 9.6/4.8 amps, 60 Hz, 3 ph. Reeves Varidrive Module, maximum ratio: 20.9, final rpm (max. ratio): 83.25 rpm. Eccentric centers for medium to high viscosity liquids. Consists of four sliding vanes with through-vane slots, large ports and pumping chamber, and open flow path for least resistance to highly viscous, hard-to-pump liquids. Steel base. Pump inlet/outlet: 3 in. 'S' line. Overall dimensions: 61 in. L x 30 in. W x 30 in. H.



