

## Cherry Burrell Stainless Steel Jacketed Batch Tank - 2500 Gallons

**Mfg: Cherry - Burrell**

**Model:**

**Stock No: SPGT038C.95**

**Serial No:**

Cherry Burrell Stainless Steel Jacketed Batch Tank. Approximate capacity: 2500 gallons. Inside dimensions: 83 in. dia. x 99 in. straight wall. Tank comes equipped with top and bottom agitators, dual spray balls, and (3) load cells. Bottom agitator dimensions (approx.): 6 ft. 2 in. L x 1 ft. W. Top agitator dimensions: 2 ft. 1 in. L x 4 in. W. Reliance Electric Motor, 5-2.5 hp, 1725/860 rpm, 575/575 V, 5.44/4.32 amps, 60 Hz, 3 phase. Final rpm: 48/24. Inlets/Outlets (product): (1) 4 in. diameter S-Line fitting, (2) 3 in. diameter S-Line fitting, (1) 1 ft. 6 in. diameter manhole with lid, (1) 4 in. diameter S-Line fitting. Inlets/Outlets (media): (12) 2 in. diameter S-Line fittings. Overall dimensions: 8 ft. 8 in. L x 7 ft. 5 in. W x 12 ft. 9 in. H.





